

INSTALLATION INSTRUCTIONS

INSTALLATION OF C-FAM-201 PRIOR TO VEHICLE INSTALLATION (PKG-FAM-1XX ONLY):

1. ASSEMBLE FLEX MOUNT (C-FAM-201), SCREWING SHAFT INTO MOUNTING BASE AS SHOWN IN ILLUSTRATION. SECURE WITH INCLUDED 10-32 SOCKET HEAD CAP SCREW AND INCLUDED ALLEN WRENCH (NOT SHOWN)
2. ATTACH FLEX MOUNT TO BRACKET WITH 3 OF 10-32 X 3/8" SCREWS AND KEPS NUTS.
3. INSTALL INCLUDED CAPS AFTER TIGHTENING HARDWARE (IF DESIRED).

VEHICLE INSTALLATION:

1. MOUNT TO FLAT SURFACE USING THE SLOTS IN THE BASE AND THE PROVIDED HARDWARE

IF MOUNTING TO A HAVIS TRACK:


1. DETERMINE LOCATION OF C-FAM-112 BRACKET AND IDENTIFY THE SLOTS IN THE TRACK TO BE USED.
2. SLIDE 1/4-20 X 3/4" HEX HEAD BOLTS INTO APPROPRIATE SLOTS IN THE TRACK.
3. PLACE C-FAM-112 OVER BOLTS.
4. INSTALL 1/4" FLAT WASHERS AND NYLOCK NUTS ONTO BOLTS.
5. POSITION AS DESIRED.
6. TIGHTEN NYLOCK NUTS.

EQUIPMENT INSTALLATION

1. ATTACH EQUIPMENT TO UPPER BALL SWIVEL OF FLEX MOUNT USING EITHER SUPPLIED #8 SCREWS AND/OR NUTS OR HARDWARE SUPPLIED WITH THE EQUIPMENT.
2. POSITION EQUIPMENT AS DESIRED.

INSTALLATION TIPS/ NOTES:

1. SWIVEL DISCS CAN BE RECONFIGURED IF DESIRED, BUT NEW CONICAL LOCKING NUTS SHOULD BE USED IF ORIGINAL NUTS HAVE BEEN REMOVED.
2. COMPLETELY TIGHTENING THE LOWER DISCS (TO LOCK IN POSITION) IS RECOMMENDED TO MINIMIZE SWIVEL/ HINGE MOVEMENT.
3. BALL MOUNT HOLE PATTERN FITS 1.19 X 1.50 (30MM X 38MM) AMPS HOLE PATTERN.
4. C-FAM-201 CAN ATTACH TO EITHER SIDE OF PLATE (AS DESIRED)



ITEM NO.	QTY.	PART NUMBER	DESCRIPTION
1	1	10-006037	BRKT, FLEX ARM MOUNT, TOP
2	1	10-006863	BASE, FLEX ARM MOUNT, UNIVERSAL/ TRAK MOUNT
5	1	C-FAM-201	FLEX ARM MOUNT, 14" LG
6	6	GSM30016	NUT 1/4-20 NYLOCK, BLK, ZP, GRD 5
7	5	GSM30160	HRDW,NUT,LOCK,5/16-24,ZINC,SP
8	6	GSM31005	WASHER, 1/4 FLAT ZP, BLACK
12	6	GSM33001	SCREW 1/4-20 x 3/4" HHCS ZP
14	3	GSM30028	NUT 10-32 KEPS ZP, BLK
15	3	GSM33117	SCREW 10-32 X 3/8 PPHMS ZP
16	4	GSM33540	SCREW 8-32 X 3/8 PTHMS ZP
17	4	GSM30027	NUT 8-32 KEPS ZP

HAVIS HAVIS, INC.		75 JACKSONVILLE RD. WARMINSTER, PA. 18974 1-800-524-9900
TITLE: INSTALLATION, UNIVERSAL AND TRAK MOUNT FLEX ARM MOUNT		
DO NOT SCALE DRAWING		
SIZE A	DWG. NO. C-FAM-112-INST	REV 12-14
WEIGHT (LB): 3.17	SCALE: 1:4	SHEET 1 OF 1